




# 26 HOLMAN 38



|             |         |          |            |
|-------------|---------|----------|------------|
| DISTANCE:   | 38 FEET | VOLUME:  | 30.6 mL    |
| RATIO:      | 2.34:1  | FORWARD: | 16 mL      |
| DROP BRUSH: | 36 FEET | REVERSE: | 14.6 mL    |
| TANKS:      | KEGEL   | PUMP:    | 50 $\mu$ L |



## FORWARD LOADS DATA

| # | START | STOP | LOADS | MICS | SPEED | BUFF | TANK      | DISTANCE | T.OIL |
|---|-------|------|-------|------|-------|------|-----------|----------|-------|
| 1 | 2L    | 2R   | 2     | 50   | 18    | 500  | A - KEGEL | 0 → 3    | 3,700 |
| 2 | 2L    | 4R   | 1     | 50   | 18    | 500  | A - KEGEL | 3 → 5    | 1,750 |
| 3 | 4L    | 4R   | 2     | 50   | 18    | 500  | A - KEGEL | 5 → 10   | 3,300 |
| 4 | 7L    | 6R   | 2     | 50   | 18    | 500  | A - KEGEL | 10 → 15  | 2,800 |
| 5 | 7L    | 7R   | 1     | 50   | 18    | 500  | A - KEGEL | 15 → 18  | 1,350 |
| 6 | 11L   | 8R   | 1     | 50   | 18    | 500  | A - KEGEL | 18 → 20  | 1,100 |
| 7 | 12L   | 9R   | 2     | 50   | 18    | 500  | A - KEGEL | 20 → 25  | 2,000 |
| 8 | 2L    | 2R   | 0     | 50   | 22    | 500  | A - KEGEL | 25 → 34  | 0     |
| 9 | 2L    | 2R   | 0     | 50   | 30    | 500  | A - KEGEL | 34 → 38  | 0     |


## REVERSE LOADS DATA

| # | START | STOP | LOADS | MICS | SPEED | BUFF | TANK      | DISTANCE | T.OIL |
|---|-------|------|-------|------|-------|------|-----------|----------|-------|
| 1 | 2L    | 2R   | 0     | 50   | 26    | 500  | A - KEGEL | 36 → 30  | 0     |
| 2 | 13L   | 11R  | 2     | 50   | 22    | 500  | A - KEGEL | 30 → 24  | 1,700 |
| 3 | 10L   | 10R  | 3     | 50   | 18    | 500  | A - KEGEL | 24 → 16  | 3,150 |
| 4 | 7L    | 8R   | 1     | 50   | 18    | 500  | A - KEGEL | 16 → 14  | 1,300 |
| 5 | 6L    | 6R   | 1     | 50   | 14    | 500  | A - KEGEL | 14 → 12  | 1,450 |
| 6 | 4L    | 4R   | 2     | 50   | 14    | 500  | A - KEGEL | 12 → 8   | 3,300 |
| 7 | 2L    | 2R   | 2     | 50   | 14    | 500  | A - KEGEL | 8 → 4    | 3,700 |
| 8 | 2L    | 2R   | 0     | 50   | 14    | 500  | A - KEGEL | 4 → 0    | 0     |

THIS PATTERN IS DESIGNED FOR:  
REVERSE DROP BRUSH

This pattern may require adjustments if using a lane machine that does not have these features

Created Jan 15, 2026 - Rendered for Atlas Pro.



SCAN QR CODE FOR  
MORE PATTERNS ON  
KEGEL PATTERN  
LIBRARY



KEGEL PATTERN LIBRARY APP



Download on the  
App Store

PATTERNLIBRARY.KEGEL.NET